STI ReSet Call Points Access Control - Series 11






PRODUCT OVERVIEW

The ReSet Call Points are a unique call point that mimic the feel of breaking glass whilst offering the user the benefits and environmental advantages of a re-settable operating element. They are safe to use in areas where glass cannot be used such as food processing plants and leisure centres. As the units can be simply reset they provide an ideal solution for areas that suffer from a high number of false activations such as schools, shopping centres and other public places.

HOW IT WORKS

The 'ReSet' uses a simple yet ingenious patented mechanism which consists of a rigid plastic operating element and an over centre spring mechanism. This arrangement provides real action on operation and simulates break glass activation. An activation indicator drops into view at the top of the window after the 'ReSet' has been operated. The unit is then simply reset with a key and is ready for reuse straight away.



Positive action - mimics the feel of breaking glass.

A warning indicator drops into view when the call point is activated. STEP 3:

To reset a simple key is inserted into the bottom of the call point. STEP 4:

A quick turn of the key and the call point is reset and ready for use again straight away.

DIMENSIONS

2111211313113			
	Width (mm)	Depth (mm)	Height (mm)
RP Flush	87	23	87
RP Surface	87	58	87
WRP2	88.63	71.9	90.26

KEY FEATURES

General Information

- · Unique manual call point that mimics the feel of breaking glass whilst offering the user the benefits and environmental advantages of a resettable operating element.
- · Three year guarantee against breakage of polycarbonate in normal use (one year guarantee on electromechanical and electronic components).

Design

- · An indicator drops into view at the top of the window on activation. The unit is then simply reset with a key and is ready for re-use straight away.
- · Waterproof models are tested to IP67.

Construction

· Extremely attractive, high value look and feel: glass appearance maintains operator deterrence. whilst a visible warning flag confirms activation.

Installation

- · Easy installation due to no glass elements that could be broken or incorrectly fitted.
- Surface mounted, 20mm conduit entry points are provided for ease of installation.
- Operating temperature -20°C (-4°F) to 65°C (149°F).

Options

- · Low profile, heavy-duty terminations.
- Optional integral cover can be fitted to prevent accidental activation.
- Complete functional test with every activation.
- · Alternative electrical arrangements available.
- · Six colours available.

Accessories:

STI RP-K Reset Key

MODELS AVAILABLE

RP-GF2-11 Reset Call Point, Flush mount in Green with Double Pole Changeover Electrical Arrangement, with Running Man Logo

RP-GD2-11 Reset Call Point, Surface mount in Green with Double Pole Changeover Electrical Arrangement, with Running Man Logo

