



Mounting hole (inch)	0.3150"
Mounting hole (metric)	8mm
Indicator type	low cost standard
Mounting type	with bezel
Bezel type	recessed
Bezel material	plastic
Bezel color	black
Bezel size	8mm
Protection	IP40
Lens type	round
Lens color	red diffused
Lens size	5mm
Connector Tpe	wire terminals 900mm
Connector number	2
Connector for lamp test	no
Number LED chip	1
Indicator color	red
Dom wave length	625nm
Peak Wave Lenght (mA)	
Op. voltage (V)	12V DC
Forward volt max.	
Rectifier	-
AC current	-
DC current	16mA
Lum in min (mcd)	
Lum in type (DC)	70mcd
Voltage tolerance (%)	10%
Op. temperature (°C)	-25°C...+60°C
Storage temperature (°C)	-25°C...+60°C
Narrative	snap in mounting
Viewing angle (°)	

Drawn : ROJ	Ch'd : ROJ	Datasheet : 19801	Print date : 05/10/06
Revision :	Revision date : 2006-03-15	Name : ROJ	Scale :



Part Number : 1980100250900
Serial Number : 19801
LEDs Indicators

ROHS Status	Yes
-------------	-----

Drawn : ROJ	Ch'd : ROJ	Datasheet : 19801	Print date : 05/10/06
Revision :	Revision date : 2006-03-15	Name : ROJ	Scale :