
RF Single Color Remote Controller


09.289SD.04166



Important: Read All Instructions Prior to Installation

Function introduction





Bottom side

Product Data


| Output | RF signal |
|-----------------------|---------------------|
| Operation Frequency | 869.5/916.5/434MHz |
| Power Supply | 4.5V(3xAAA battery) |
| Operating temperature | 0-40°C |
| Relative humidity | 8% to 80% |
| Dimensions | 120x55x17mm |

- · Control 4 zones of RF receivers separately.
- Single color controller
- High sensitive & high stable, fast & precise color control.
- Compatible with all universal series RF receivers
- 1 receiver can be paired by max 8 different remote controls.
- Waterproof grade: IP20


Safety & Warnings

- This device contains AAA batteries that shall be stored and disposed properly.
- DO NOT expose the device to moisture.


Pair with RF receiver(Method 1)



Pair with RF receiver(Method 2)



Save color/scene/mode



Recall the saved colors/scenes

