

SlimPAR 56 ILS

- LED Par designed for any application in need of a compact wash light
- ILS compatibility for use in the ILS ecosystem
- D-Fi™ USB compatibility for wireless Master/Slave or DMX control
- Convenient access to RGB color mixing and static colors without DMX
- Trigger eye-catching effects with built-in automated programs via Master/Slave or DMX mode
- Save time running cables and extension cords by power linking multiple units
- Easily transports in the optional CHS-SP4 VIP Gear Bag



Specifications

- DMX Channels: 3 or 7
- DMX Connectors: 3-pin XLR
- Light Source: 108 LEDs (36 red, 36 green, 36 blue) 0.25 W (20 mA), 50,000 hours life expectancy.
- Strobe Rate: 0 to 20 Hz
- Beam Angle: 14°
- Field Angle: 23°
- Luminance : 1,337 lux @ 2 m
- Power Linking: 50 units @ 120 V; 83 units @ 230 V
- Input Voltage: 100 to 240 VAC, 50/60 Hz (auto-ranging)
- Power and Current: 11 W, 0.1 A @ 120 V, 60 Hz
- Power and Current: 11 W, 0.1 A @ 230 V, 50 Hz
- Bracket Mounting Hole: 13 mm
- Weight: 2.2 lbs (1 kg)
- Size: 9.7 x 11.1 x 2.5 in (246 x 282 x 64 mm)
- Optional Controllers: ILS Command
- Approvals: CE, RoHS, MET

