

Pinspot Q1Z ILS

- Compact pinspot fitted with a 20W quad-color RGBW LED
- Manual zoom for short or long throw applications
- ILS compatibility for use in the ILS ecosystem
- D-Fi USB® compatibility for wireless master/slave or DMX control
- Easy navigation and access to all functions directly from the OLED display
- Convenient, wireless non-DMX control using the IRC-6 remote
- Fits best in the CHS-40 VIP Gear Bag



Specifications

- DMX Channels: 4, 6, or 7
- DMX Connectors: 3-pin XLR
- Light Source: 1 LED (quad-color RGBW) 20 W, (5.3A), 50,000 hours life expectancy
- Strobe Rate: 0 to 33 Hz
- Zoom Angle (manual): 5° to 25°
- Illuminance (narrow): 4,081 lux @ 2 m
- Illuminance (Wide): 623 lux @ 2 m
- Lumens: 617
- Input Voltage: 100 to 240 VAC, 50/60 Hz (auto-ranging)
- Power and Current: 19 W, .3 A @ 120 V, 60 Hz
- Power and Current: 20 W, .2 A @ 230 V, 50 Hz
- Bracket Mounting Hole: M12
- Weight: 3 lb (1.36 kg)
- Size: 12.1 x 3.5 x 8.5 in (308 x 89 x 217 mm)
- Optional Controllers: IRC6, ILSCOMMAND
- Approvals : CE, UKCA, ROHS

