

"All statements, technical information and recommendations contained herein are based on tests we believe to be reliable, but the accuracy or completeness thereof is not guaranteed. The results reported herein are based solely on the limited sample provided to us for testing under laboratory conditions and are NOT intended to be representative of typical product performances.

3M shall not be liable in tort or in contract for any injury, loss or damage, direct, indirect, special or consequential, arising out of the use of or the inability to use the product. Before using, user shall determine the suitability of the product for user's intended use, and user assumes all risks and liability whatsoever in connection therewith."

3M 577F Cubicut™ Polycut™ Resin Bond Cloth

Product	577F
Construction	P-graded Alumina-Zirconia mineral is coated on a strong Y weight polyester backing. A grinding aid supersize is also included. Available in grades P24, P36, P40, P50, P60, P80, P100, P120, P150 and P180.
Application Areas	Moderate grinding pressures requiring backing strength. Works very well on stainless steel and other exotic alloys.
Features	Best suited to off-hand grinding.
Max. Available Width	52 in (1320.8 mm)

Available Converted Forms (*)

Belts

- * Regular
- Segment
- Clipped

Discs

- * Regular
- Roloc™
- Delappe
- Overlap slotted

Evenrun

- Bands
- Belts

Rolls

- * Regular
- Scored
- Serrated
- Slit down
- * Cartridge

Stikit™

- Disc/roll
- Sheet/roll
- Refill rolls
- Individual discs
- Individual sheets

Other

- PG wheels
- * RX segments
- Slashed assemblies
- Sheets
- Cones