

## Selectable Power Supply

### Overview

12 or 24vdc power supply  
8 or 4 amps of power



- Input: 100~240Vac 50~60Hz
- Main Fuse: F3A
- Mains Output 12V Mode: 13.2~14.0vdc (13.8vdc nominal), Max 8A
- Mains Output 24V Mode : 27.0~28.0vdc, (27.6vdc nominal), Max 4A
- Battery Output 12V Mode: 10.5~12.4vdc
- Battery Output 24V Mode: 21.0 ~ 24.7vdc
- Additional Outputs: Mains and Independent relays
- Charge current: 0.7A max
- Charger fuse: 0.5A PTC
- Panel Indicators: Mains/Fault
- Output Fuse: F8A @12v default, change to F4A @24v
- Number of Outputs: 1 x 8 amp in 12v mode
- Protection: Over-current/ Over-load/ Over-charge/Over-discharge
- Battery Capacity: 2 x 12v/ 7Ah Max
- Tamper: Front and Rear
- Dimensions: W 330 x H 365 x D 85 mm
- Warranty: 3 Years
- Accessories: Fuses 1x8A, 1x4A, 1x3A, 1x2A  
1x PG11 Gland, 2x M20 Rubber Feet, 4x Plastic Sticky Feet 1x pair of  
Battery Leads and 1x Battery Jumper Lead