

TV Wall Mount for up to 80 inch (110lb) VESA Mount Displays - Low Profile Full Motion Universal TV Wall Mount Bracket - Heavy Duty Adjustable Tilt/Swivel Articulating Arm

Product ID: FPWARTS1



With its contemporary design, featuring a long extension arm with a large swivel range, this full motion TV wall mount for large-screen displays is the perfect choice for versatile viewing. You can extend the swiveling arm out to adjust your screen position, making it easy to view your display from numerous angles within the room.

This adjustable wall mount TV bracket is ideal for a meeting space, lobby, boardroom, classroom or other venues. The monitor mount provides an impressive and secure way to display a flat-panel TV or mount a digital signage display, while freeing up valuable space.

Engineered from high-grade steel, the flat-screen TV wall mount securely supports VESA mount displays, including curved TVs, 37" to 80" with a weight capacity of 110 lb. (50 kg).

With a smooth and effortless motion, you can extend the articulating arm out from the wall up to 25.5" (65 cm) to adjust the position of your display. Swivel the arm with ease, up to 90 degrees to the left or right, to position your TV for comfortable viewing.

You can also retract the arm back, to nest against the wall. With its low-profile design, the articulating TV wall mount enables your display to sit just 2.8" (70 mm) from the wall.

Swivel your screen +/- 90 degrees and tilt your screen -2 to +15 degrees for ideal viewing and to reduce glare.

The tilting TV wall mount also has a screen level adjustment, so you can adjust your display up to 3 degrees clockwise or counterclockwise after you've installed it, to ensure your display is level.

The universal swivel TV wall mount is easy to install. The television mounting brackets for flat screen displays feature a post-installation lateral shift, to help adjust and center the mount on the wall, even with off-center studs. Cable management keeps cables neatly organized.

FPWARTS1 is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Securely wall-mount your TV for easy viewing in boardrooms, lobbies, classrooms and meeting spaces
- Keep guests informed in hotels, restaurants and other venues
- Save space by wall-mounting your TV in your home theater

Features

- **LARGE 80" TV WALL MOUNT:** This heavy-duty TV wall mount supports VESA compatible displays incl. curved TVs up to 80 inch (110 lb/50 kg) w/ a durable full-motion steel frame and a powder-coated finish
- **WIDE RANGE OF MOTION:** Articulating TV wall mount offers +/-90 swivel, +2/-15 tilt & +/-3 LCD screen level adjustment & arms allow low-profile at 2.8" (70 mm) from wall or extend to 25.5" (650 mm)
- **LATERAL ADJUSTMENT:** Full motion TV wall mount w/ post-install lateral shifting lets you center the display on a wall or corner, w/ 16"/24" off-centered studs w/ range of 45.8"/1.1m from left to right
- **COMPATIBILITY:** Universal TV wall mount supports LG, Samsung, Sony, Sharp, among others (screws/spacers incl) & VESA hole patterns 200x100, 200x200, 200x300, 200x400, 300x200, 300x300, 400x200, 400x300, 400x400, 600x200, 600x300, 600x400
- **TIDY AESTHETIC:** The adjustable tv wall mounting bracket w/ integrated cable management & optional black snap-on covers keeps flat screen cables organized; ideal for customer-facing digital signage

Hardware

Warranty	5 Years
Wallmountable	Yes
Cable Management	Yes
Articulating	Yes
# of Displays Supported	1
Mounting Options	Wall-Mount
Minimum Profile from Wall	2.8 in [70 mm]

VESA Hole Pattern(s)	200x100 mm
	200x200 mm
	200x300 mm
	200x400 mm
	300x200 mm
	300x300 mm
	400x200 mm
	400x300 mm
	400x400 mm
	600x200 mm
	600x300 mm
	600x400 mm

Performance

General Specifications	Screen Level Adjustment: +3 / -3
Weight Capacity (Per Display)	110.2 lb [50 kg]
Minimum Display Size	37"
Maximum Display Size	80"
Fits Curved Display	Yes
Minimum Arm Extension	2.8 in [70 mm]
Maximum Arm Extension	25.6 in [650 mm]
Display Tilt	+2 / -15
Display Swivel	+90 / - 90
Swivel / Pivot	+90 / -90

Physical Characteristics

Color	Black
-------	-------

Material	Steel
Product Length	25.6 in [650.0 mm]
Product Width	18.3 in [46.5 cm]
Product Height	36.8 in [93.5 cm]
Weight of Product	458.9 oz [13000.0 g]

Packaging Information

Package Quantity	1
Package Length	28.7 in [73.0 cm]
Package Width	21.5 in [546.0 mm]
Package Height	3.9 in [9.8 cm]
Shipping (Package) Weight	31.5 lb [14.3 kg]

What's in the Box

Included in Package	1 - TV Wall Mount Assembly
	1 - Wall Mounting Bracket
	2 - TV Mounting Brackets
	2 - Decorative Covers
	2 - Mounting Plates
	4 - M6 x 15 mm Screws
	4 - Round Washers, Small
	1 - Wrench
	1 - Hex Key
	4 - M5 x 14 mm Screws
	4 - M6 x 14 mm Screws
	4 - M6 x 30 mm Screws
	4 - M8 x 30 mm Screws

4 - M8 x 50 mm Screws

4 - Rectangular Washers

8 - Small Spacers

8 - Large Spacers

6 - Mounting Screws

6 - Wall Anchors

6 - Round Washers, Large

1 - User Manual

****Product appearance and specifications are subject to change without notice.***