



This item includes:

 Item No.: 221-412 Splicing connector with levers; for all conductor types; max. 4 mm ² ; 2-conductor; transparent housing; Surrounding air temperature: max 85°C (T85); 4,00 mm ² ; transparent	 Item No.: 221-413 Splicing connector with levers; for all conductor types; max. 4 mm ² ; 3-conductor; transparent housing; Surrounding air temperature: max 85°C (T85); 4,00 mm ² ; transparent	 Item No.: 221-415 Splicing connector with levers; for all conductor types; max. 4 mm ² ; 5-conductor; transparent housing; Surrounding air temperature: max 85°C (T85); 4,00 mm ² ; transparent	 Item No.: 2273-203 PUSH WIRE® splicing connector; for solid conductors; max. 2.5 mm ² ; 3-conductor; transparent housing; orange cover; Surrounding air temperature: max 60°C (T60); 2,50 mm ² ; transparent
 Item No.: 2273-205 PUSH WIRE® splicing connector; for solid conductors; max. 2.5 mm ² ; 5-conductor; transparent housing; yellow cover; Surrounding air temperature: max 60°C (T60); 2,50 mm ² ; transparent	 Item No.: 2273-208 PUSH WIRE® splicing connector; for solid conductors; max. 2.5 mm ² ; 8-conductor; transparent housing; light gray cover; Surrounding air temperature: max 60°C (T60); 2,50 mm ² ; transparent	 Item No.: 2273-500 Mounting carrier; for single- and double-row con.; 2273 Series; for DIN-35 rail mounting/screw mounting; orange	 Item No.: 221-500 Mounting carrier; 221 Series - 4 mm ² ; for DIN-35 rail mounting/screw mounting; orange

Notes

Safety management note

NOTICE: Observe installation and safety instructions!

- Only to be used by electricians!
- Do not work under voltage/load!
- Use only for proper use!
- Observe national regulations/standards/guidelines!
- Observe technical specifications for the products!
- Observe the number of permissible potentials!
- Do not use damaged/dirty components!
- Observe conductor types, cross-sections and strip lengths!
- Insert conductor until it hits the product's backstop!
- Use original accessories!

To be sold only with installation instructions!



Physical data		
Width		259 mm / 10.197 inches
Height		42 mm / 1.654 inches
Depth		106 mm / 4.173 inches

Material data		
Note (material data)		Information on material specifications can be found here
Fire load		5.368 MJ
Weight		412.8 g

Commercial data		
ETIM 9.0		EC000446
ETIM 8.0		EC000446
PU (SPU)		1 pcs
Packaging type		Box
Country of origin		DE
GTIN		4066966083958
Customs tariff number		85369010000

Environmental Product Compliance		
RoHS Compliance Status		Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 887-802

↓