



Color: silver-colored

Technical data	
Suitable	for push-button frame (210-853)
Marking method	Thermal transfer
Marking	plain
Delivery form	Roll
Delivery form configuration	350 markers/reel; 1 line
Printing device	Smart Printer (thermal transfer printer)

Physical data	
Height	27 mm
Width	19 mm
Depth	0.65 mm
Marking surface	27 x 19 mm

Mechanical data	
Mounting type	Sticking
Smear resistance	in conjunction with 258-5005 Ink Ribbon

Material data	
Color	silver-colored
Material	Polyester
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	Acrylic; permanent; foamed
Halogen-free	Yes
Weight	110 g
Fire load	0 MJ



Environmental requirements	
Ambient temperature (storage)	≥+22 °C
Ambient temperature (operation)	-30 ... +130 °C
Relative humidity	40 ... 50 %

Commercial data	
Product Group	2 (Terminal Block Accessories)
eCl@ss 10.0	27-40-06-29
eCl@ss 9.0	27-40-06-29
ETIM 9.0	EC001288
ETIM 8.0	EC001288
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4050821674924
Customs tariff number	39199080888

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 210-852

↓

Documentation

Operating Instructions

210-852 Information on handling print material

1

28.08.2020

pdf

1004.72 KB

↓

1 Compatible Products

1.1 Required Accessories

1.1.1 Marking

1.1.1.1 Frame

Item No.: 210-853

Universal push-button border; halogen-free; black



1.2 Optional Accessories
1.2.1 Marking
1.2.1.1 Marking device



Item No.: 258-5000
Thermal transfer printer; Smart Printer; for complete control cabinet marking; 300 dpi; With marking material