



Product number 1171253340
EAN 4007123685462

DESCRIPTION

- LED Light with extra bright Everlight SMD LEDs.
- Solid and modern aluminium casing.
- Stable, foldable frame with plastic protective corners and ergonomically shaped plastic carrying handle.
- Steplessly pivotable light which can be locked with one hand by means of a quick-release fastener.
- With safety glass.

TECHNICAL DATA

Cable quality	Rubber-Neoprene
Luminous flux	3450 lm
Power consumption	30 W
Luminous efficacy	136 lm/W
Energy efficiency class	
Min.-Max. Nominal input voltage	220 V - 240 V

Cable length	3 m
Cable designation	H07RN-F 3G1,0
Impact strength	IK08
Protection class	I
Degree of protection (IP)	IP65
Colour	black

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1
Weight of product (without packaging)	1.41 kg
Dimension LxWxH (without packing)	8 cm x 24.5 cm x 27.5 cm

Weight of product (including packaging)	1.62 kg
Dimension LxWxH (incl. packing)	11.5 cm x 27.2 cm x 28 cm

SCOPE OF DELIVERY

LED Work Light JARO 4063 M