



Pushing Performance  
Since 1945

# Han Protect 3A HTE M12 4/4 Fused



Image is for illustration purposes only. Please refer to product description.

Part number	10 81 007 1144
Specification	Han Protect 3A HTE M12 4/4 Fused
HARTING eCatalogue	<a href="https://b2b.harting.com/10810071144">https://b2b.harting.com/10810071144</a>

## Identification

Category	Connector sets
Series of hoods/housings	Han® Protect
Type of hood/housing	Hood

## Version

Termination method	Crimp termination
Gender	Male
Size	3 A
Number of contacts	4
further contacts	4 Contacts fused
PE contact	Yes
Version	Top entry
Locking type	Single locking lever
Field of application	Fusing I/O signals

## Technical characteristics

Rated current	4 A
Rated voltage	24 V
Limiting temperature	-25 ... +70 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP54



**Pushing Performance**  
Since 1945

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR Polyethylen (PE)
Material (locking)	Polycarbonate (PC)
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	CE UKCA

## Commercial data

Packaging size	10
Net weight	0.1 g
European customs tariff number	85366990
GTIN	5713140435032
eCl@ss	27440113 Rectangular connectors (set)