

RF Inductor-Wirewound



BWS25GRF0-KIT JIS 2520 Size

Designer Kit Contents

Pulse - Std Power Part Number	L (mm)	W(mm)	T (mm)	SIZE Code (JIS/EIA)	Inductance (nH)	Tolerance (±%)	RDC(Ω) Max.	IDC(mA)Max.	Quantity
BWCS0029282110NG00	2.9	2.7	2.1	2520/1008	10	2	0.08	1000	20
BWCS0029282112NG00	2.9	2.7	2.1	2520/1008	12	2	0.09	1000	20
BWCS0029282115NG00	2.9	2.7	2.1	2520/1008	15	2	0.1	1000	20
BWCS0029282118NG00	2.9	2.7	2.1	2520/1008	18	2	0.11	1000	20
BWCS0029282122NG00	2.9	2.7	2.1	2520/1008	22	2	0.12	1000	20
BWCS0029282127NG00	2.9	2.7	2.1	2520/1008	27	2	0.13	1000	20
BWCS0029282133NG00	2.9	2.7	2.1	2520/1008	33	2	0.14	1000	20
BWCS0029282139NG00	2.9	2.7	2.1	2520/1008	39	2	0.15	1000	20
BWCS0029282147NG00	2.9	2.7	2.1	2520/1008	47	2	0.16	1000	20
BWCS0029282156NG00	2.9	2.7	2.1	2520/1008	56	2	0.18	1000	20
BWCS0029282168NG00	2.9	2.7	2.1	2520/1008	68	2	0.2	1000	20
BWCS0029282182NG00	2.9	2.7	2.1	2520/1008	82	2	0.22	1000	20
BWCS00292821R10G00	2.9	2.7	2.1	2520/1008	100	2	0.56	650	20
BWCS00292821R12G00	2.9	2.7	2.1	2520/1008	120	2	0.63	650	20
BWCS00292821R15G00	2.9	2.7	2.1	2520/1008	150	2	0.7	580	20
BWCS00292821R18G00	2.9	2.7	2.1	2520/1008	180	2	0.77	620	20
BWCS00292821R20G00	2.9	2.7	2.1	2520/1008	200	2	0.84	500	20
BWCS00292821R22G00	2.9	2.7	2.1	2520/1008	220	2	0.84	500	20
BWCS00292821R27G00	2.9	2.7	2.1	2520/1008	270	2	0.91	500	20
BWCS00292821R33G00	2.9	2.7	2.1	2520/1008	330	2	1.05	450	20
BWCS00292821R39G00	2.9	2.7	2.1	2520/1008	390	2	1.12	470	20
BWCS00292821R47G00	2.9	2.7	2.1	2520/1008	470	2	1.19	470	20
BWCS00292821R56G00	2.9	2.7	2.1	2520/1008	560	2	1.33	400	20
BWCS00292821R62G00	2.9	2.7	2.1	2520/1008	620	2	1.4	300	20
BWCS00292821R68G00	2.9	2.7	2.1	2520/1008	680	2	1.47	400	20
BWCS00292821R75G00	2.9	2.7	2.1	2520/1008	750	2	1.54	360	20
BWCS00292821R82G00	2.9	2.7	2.1	2520/1008	820	2	1.61	400	20
BWCS00292821R91G00	2.9	2.7	2.1	2520/1008	910	2	1.68	380	20
BWCS00292821R0G00	2.9	2.7	2.1	2520/1008	1000	2	1.75	370	20
BWCS00292821R2G00	2.9	2.7	2.1	2520/1008	1200	2	2	310	20
BWCS00292821R5G00	2.9	2.7	2.1	2520/1008	1500	2	2.3	330	20
BWCS00292821R8G00	2.9	2.7	2.1	2520/1008	1800	2	2.6	300	20
BWCS00292821R2G00	2.9	2.7	2.1	2520/1008	2200	2	2.8	280	20
BWCS00292821R7G00	2.9	2.7	2.1	2520/1008	2700	2	3.2	290	20
BWCS00292821R3G00	2.9	2.7	2.1	2520/1008	3300	2	3.4	290	20
BWCS00292821R9G00	2.9	2.7	2.1	2520/1008	3900	2	3.6	260	20
BWCS00292821R4R7G00	2.9	2.7	2.1	2520/1008	4700	2	4	260	20
BWCS00292821R5R6G00	2.9	2.7	2.1	2520/1008	5600	2	4	240	20
BWCS00292821R6R8G00	2.9	2.7	2.1	2520/1008	6800	2	4.9	200	20
BWCS00292821R8R2G00	2.9	2.7	2.1	2520/1008	8200	2	6	170	20
BWCS00292821R00G00	2.9	2.7	2.1	2520/1008	10000	2	8	150	20
BWCS00292821R50G00	2.9	2.7	2.1	2520/1008	15000	2	11	100	20

RF Inductor-Wirewound



BWS25GRF0-KIT JIS 2520 Size

Dimensions – Millimeters (Inches)

