

6.6ft (2m) USB-C Cable, USB 5Gbps, 100W (5A) Power Delivery, 4K 60Hz DP Alt Mode, TPE Jacket - Thunderbolt Compatible

**Product ID:** USB315CCV2M



This USB 3.2 Gen1 5Gbps USB-C cable lets you connect your USB Type-C devices for syncing, charging and powering your devices.

The cable is also compatible with Thunderbolt 3 ports, which means you can charge and sync your USB-C mobile devices using your Thunderbolt 3 laptop.

#### Power your USB-C devices

With up to 5A (100W) of power delivery, you can power a USB-C laptop, such as your Apple MacBook or Microsoft Surface Book. Simply connect the cable to your USB-C laptop and to a USB-C wall charger.

You can use this USB Type-C cable to power your USB-C hard drive from the USB-C port on your laptop.

#### Deliver 8K video with DisplayPort 1.4 Alt Mode

The cable supports 8K 30Hz video with DisplayPort 1.4 and is backward compatible to connect your docking station or laptop to a monitor that supports 4K or 1080p resolutions.

#### Charge your mobile devices

When used with devices that support PD 3.0, this cable charges up to 20V and 5A for a maximum of 100W. It can decrease your charge time and make sure your mobile devices are ready, whenever you need them.

## Certifications, Reports and Compatibility



## Applications

## Features

- **HIGH PERFORMANCE:** 6.6ft (2m) USB-C cable supports USB 3.2 Gen 1 SuperSpeed (5Gbps) data transfer; DisplayPort 1.4 Alt mode up to 4K 60Hz; This USB C to C cable supports up to 100W (5A) Power Delivery 3.0 charging; Thunderbolt 3 compatible
- **HIGH QUALITY CONSTRUCTION:** For home or office, this high quality USB C Cord has been tested to meet USB 3.2 Gen 1 standards; 32 AWG conductors with Al-Mylar foil (85% Braid coverage) EMI shielding provides superior signal integrity and reliability
- **DURABLE DESIGN:** USB Type-C cable has been tested to withstand 10,000+ insertions & 4000+ bend angle of +/- 60 Long lasting flexible TPE jacket and strain relief; TPE is non-toxic and halogen free; Compatible with USB 3.2 Gen 1 and earlier versions
- **APPLICATIONS:** Works w/docking stations/external hard drives; TB3/4 or USB-C laptops MacBook Air/Pro, Surface Book, X1 Carbon, iPad Pro, iPhone 15 [Plus/Pro/Max] and up, Samsung Galaxy S8 & up, Pixel 5; USB-C portable monitors Asus ZenScreen/ProArt
- **SPECS:** 6.6 feet (2 meter); Color: Black; USB 3.2 Gen 1 5Gbps; PD 3.0, 20V (max), 5A (max); USB C Cable Male to Male; 0.19" (4.8 mm) Outer Diameter, 32 AWG; Jacket: TPE; EMI Shield: Al-Mylar Foil, 85% Braid; DP 1.4 Alt mode 8K 30Hz

### Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

### Performance

Maximum Digital Resolutions	8K @ 30Hz
Type and Rate	USB 3.2 Gen 1 - 5 Gbit/s

### Connector(s)

Connector A	1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps)
	1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps)

---

**Power**

Power Delivery	100W
----------------	------

---

**Physical Characteristics**

Color	Gray and Black
Wire Gauge	30/32 AWG
Cable Length	78.7 in [2000 mm]
Cable OD	0.2 in [4.8 mm]
Product Length	6.6 ft [2.0 m]
Product Width	0.5 in [1.2 cm]
Product Height	0.3 in [6.5 mm]
Weight of Product	2.9 oz [82.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.5 in [1.2 cm]
Shipping (Package) Weight	4.2 oz [120.0 g]

---

**What's in the Box**

Included in Package	1 - 2m USB-C 5Gbps cable
---------------------	--------------------------

---

***\*Product appearance and specifications are subject to change without notice.***