

# PRODUCT SPECIFICATION

**Carl  
Kammerling**  
International

|                         |               |
|-------------------------|---------------|
| <b>Brand</b>            | C.K           |
| <b>Product Range</b>    | Feeler Gauges |
| <b>Catalogue number</b> | 3961A         |
| <b>Date</b>             | 18/02/2009    |

|   |                             |   |                       |                   |
|---|-----------------------------|---|-----------------------|-------------------|
| <b>Range Description</b><br>Professional quality feeler gauges  |                             |   |                       |                   |
| <b>Features</b><br><br><b>3525, 3525M</b> <ul style="list-style-type: none"> <li>• Precision ground steel blades</li> <li>• Permanently etched sizes on blades</li> <li>• Blades fold into protective metal case</li> </ul> |                             |  |                       |                   |
| <b>Item Number</b>  | <b>Item Description</b>     | <b>EAN No</b>   | <b>Commodity code</b> | <b>Carton Qty</b> |
| T3525 413   | Feeler Gauge 4" 13 Blade    | 5013969479607   | 82055910              | 3                 |
| T3525M 413  | Feeler Gauge 100mm 13 Blade | 5013969479805   | 82055910              | 3                 |

|                                    |  |
|------------------------------------|--|
| Technical product information      | <b>Sizes</b><br>3525 – 2, 3, 4, 5, 6, 8, 10, 12, 15, 20, 25, 30 & 35 thousandths of an inch<br>3525M - 0.05, 0.1, 0.2, 0.25, 0.3, 0.4, 0.5, 0.6, 0.7, 0.8, 0.9 & 1mm |
| Standards compliance               | None applicable  |
| User health and safety information | Non applicable   |
| RoHS/WEEE compliance               | This product range does not fall within the scope of RoHS or WEEE regulations  |
| Material safety data               | None applicable  |
| Warranty                           | C.K Tools are guaranteed for life against imperfect materials or workmanship<br>Normal wear and tear or damage caused through inappropriate use is not covered       |
| Country of origin                  | Germany  |

## Dimensional details

| Item       | Product only |          |           |              | Product on primary packaging |          |           |                |
|------------|--------------|----------|-----------|--------------|------------------------------|----------|-----------|----------------|
|            | Width mm     | Depth mm | Height mm | Net weight g | Width mm                     | Depth mm | Height mm | Gross weight g |
| T3525 413  | 15           | 6        | 105       | 44           | 45                           | 20       | 180       | 54             |
| T3525M 413 | 15           | 6        | 105       | 44           | 45                           | 20       | 180       | 54             |

| Item       | Shelf box (secondary packaging) |          |           |                | Euro Pallet data<br>Wi x Hi |                     |
|------------|---------------------------------|----------|-----------|----------------|-----------------------------|---------------------|
|            | Width mm                        | Depth mm | Height mm | Gross weight g | No of cartons on base       | Number of rows high |
| T3525 413  | 80                              | 25       | 190       | 164            |                             |                     |
| T3525M 413 | 80                              | 25       | 190       | 164            |                             |                     |

## Packaging waste details

| Item       | Primary Packaging |        |        |     | Secondary packaging |     |        |     |
|------------|-------------------|--------|--------|-----|---------------------|-----|--------|-----|
|            | Plastic g         | Use    | Card g | Use | Plastic g           | Use | Card g | Use |
| T3525 413  | 10                | Hanger |        |     | 3                   | Bag |        |     |
| T3525M 413 | 10                | Hanger |        |     | 3                   | Bag |        |     |