

SBBTH127P *Proto Advantage*

Datasheet revision 1.0

www.Proto-Advantage.com

Solder-in breadboard 2x2" 1.27mm pitch plated holes

Product Highlights

Plated through hole solder breadboard
Immersion Gold (ENIG) Finish
Double Sided
1443 pads in total
Plated through hole pads on 1.27mm matrix
Hole pitch of 1.27mm center-to-center
37 rows, 39 columns

Specifications

Dimensions:	2.0" x 2.0" x 0.0625"
PCB construction:	FR-4 UL94V-0
PCB operating temperature range:	-40°C to +130°C
PCB reflow maximum temperature:	+260°C
Pad size:	Round: 1.0mm (0.039") diameter
Pad pitch:	1.27mm center-to-center
Space between pads:	0.27mm (0.011")
Holes:	0.64mm (0.025") in diameter

