

Eaton E50AR1

Catalog Number: E50AR1

Eaton E50 NEMA heavy duty plug-in limit switch,Assembly,Screw Terminals,10A at 240 Vac,1A at 250 Vdc,E50DR1,E50DR1,Side rotary,1NO-1NC,Die cast zinc,NEMA 1,3,3S,4,4X,6,6P,13,IP67,10A continuous,1A,10° to 200°F,E50 Heavy Duty Plug In



General specifications

Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit switch	E50AR1
	UPC
	782113289861
Product Length/Depth	Product Height
4.22 in	2.46 in
Product Width	Product Weight
1.54 in	1.2 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
CSA Certified	
UL Listed	

Product specifications

Type

Assembly

Contact Rating

10A at 240 Vac, 1A at 250 Vdc

Enclosure material

Die cast zinc

Accessories

E50DR1

Actuator

Side rotary

Connection

Screw terminal

Contact configuration

1 NO-1 NC

Series

E50 heavy duty plug in

Operating temperature - max

200 °F

Operating temperature - min

10 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67

Maximum AC current

10 A continuous

Maximum DC current

1 A

Resources

Specifications and datasheets

[Eaton Specification Sheet - E50AR1](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)