

Eaton C25DNF340A

Catalog Number: C25DNF340A

Eaton definite purpose contactor, Quick, Class J, 600V, 60A, 40A, 110-120 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and 3P, 40A, Contactor, 3P, 50A, Box lugs (posidrive setscrew) and quick connect terminals , Non-reversing



General specifications

Product Name	Catalog Number
Eaton definite purpose contactor	C25DNF340A
UPC	Product Length/Depth
782116300662	3.35 in
Product Height	Product Width
3.75 in	2.4 in
Product Weight	Warranty
0.9 lb	1 year
Compliances	Certifications
RoHS Compliant	CSA Certified
	UL Recognized

Product specifications

Amperage Rating

40A

Number Of Poles

Three-pole

Type

Non-reversing

Coil

110-120 Vac, 50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

40 A

Model

Contactor

Resistive load

50 A

Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

Connection

Quick

Resources

Specifications and datasheets

[Eaton Specification Sheet - C25DNF340A](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)