

UIC 558 18PIN PLUG KIT-MC-AG-CND



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 018 1022
Specification	UIC 558 18PIN PLUG KIT-MC-AG-CND
HARTING eCatalogue	https://b2b.harting.com/09580181022

Identification

Category	Connector sets
Series	HARTING UIC
Identification	UIC 558
Element	Connector sets

Version

Termination method	Crimp termination
Gender	Male
Number of contacts	18
Number of cable entries	1
Cable entry	1x Pg 21
Details	Crimp contacts enclosed separately Please order conduit parts separately.

Technical characteristics

Conductor cross-section	0.75 ... 1 mm ²
Conductor cross-section [AWG]	AWG 18 ... AWG 17
Rated current	10 A
Rated voltage	60 V
Insulation resistance	>10 ⁷ Ω
Contact resistance	≤4 mΩ
Stripping length	5 mm
Limiting temperature	-50 ... +125 °C



Pushing Performance
Since 1945

Technical characteristics

Mating cycles	≥10,000
Degree of protection acc. to IEC 60529	IP69 / IPX9K acc. to ISO 20653 mated condition

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	Black RAL 3020 (traffic red)
Material (seal)	Silicone
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	UIC 50558 IRS 50558 IEC 61373 Category 2 IEC 60529
----------------	---

Commercial data

Packaging size	1
Net weight	210 g
Country of origin	India
European customs tariff number	85366990
GTIN	5713140190252
ETIM	EC002635
eCl@ss	27440115 Circular connector (set)