

# ZV810N

## Motion Sensor PIR Light Switch

### Features & Benefits

- ON/OFF/AUTO slide switch function (Switch can be enabled or disabled)
- Replaces existing One or Two Way light switches - 2-Wire
- Supplied with 9V battery
- Concealed front panel with retaining screw
- Red LED motion indication
- Adjustable time ON setting
- Adjustable lux (Light level) setting



### Technical Data

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	Surface
Earth Class Rating	Class II
Operating Temperature	0°C to 40°C
Ingress Protection Rating	IP20
Connection	2-Wire
Battery Type	9V Battery (Replaceable)
Power Reserve	Depends On Usage
Approved Mounting Height (m)	1.1
Back Box Minimum Depth (mm)	25
Motion Detection (m)	8 Front, 4 Side
Detection Angle	170°

# Data sheet

## ZV810N

Light / Automatic Light Switches

Switch Type	Two Way
Number Of Channels	1
Switch Rating	400W LED, 250W Fluorescent, CFL (Low-loss or Electronic Ballast), 2000W Halogen
ON Time Adjustment	10 Seconds - 15 Minutes
LUX Level	1 to 10
Permanent ON Facility	Yes (Slider Switch)
Multiple Unit Support	Yes (2 Units)
Cable Entry(s)	Back Entry

### General

Weight (g)	150
Height (mm)	86
Width (mm)	86
Depth (mm)	38
Protruding Depth (mm)	29.5
Body Construction	Polycarbonate
Product Colour	White
EAN Number	5012483015049
Guarantee Period	3 Years
Trade Tariff Commodity Code	8536508090

## Line Diagrams

