



Description

DM 41 is a compact two way speaker designed for constant voltage systems. The speaker provide natural, smooth sound reproduction ideal for use in business music systems and indoor/outdoor background music applications. Connections to the loudspeaker line are made by using the two wire cable coming out from the loudspeaker rear side. The enclosure includes a protective perforated grille and an accessory for the wall mounting.

Features

- > 3.5" woofer with 1" dome tweeter
- \rightarrow Power selectable (100 V): 15 W 7.5 W 5 W 2.5 W 1.25 W
- > 87 dB sensitivity
- > Colour white RAL 9002 and black RAL 9005
- > Plastic body UL 94 VO, steel grille
- > Protection grade IP 55

Part Number


13000049 DM 41 13000387 DM 41 B 80hm 80hm White - RAL 9002 EAN 8024530004941 Black - RAL 9005 EAN 8024530010348




DM 41

TWO-WAY COMPACT SPEAKER

Line Art 2D





TECHNICAL SPECIFICATIONS

Acoustical specifications

Frequency Response (-10dB) 100 Hz ÷ 20000 Hz

Max SPL @ 1m102 dBHorizontal coverage angle180°Vertical coverage angle170°System Sensitivity87 dB

 Power section
 Amplification
 Full Range

 Nominal Impedance
 8 ohm

 Power Handling
 15 W

Peak Power Handling 60 W PEAK Crossover Frequencies 2.5 Hz

Recommended Amplifiers DMA 162, DMA 82, DMA 162P, ES 2160, ES 3080, AM 2320, AM

2160, AM 2080, AM 1125, UP 8502, UP 8501, UP 2321, UP 2162

TransducersDome Tweeter1 x 1.0"Woofer1 x 3.5"

Input/Output sectionInput connectorsCableOutput connectorsCable

Constant Voltage Transformer

Power selection 1

Power selection 2

Power selection 3

100 V

15 W - 667 ohm

7.5 W - 1333 ohm

5 W - 2000 ohm

Power selection 35 W - 2000 ohmPower selection 42.5 W - 4000 ohmPower selection 51.25 W - 8000 ohm

Standard compliance | IP protection grade | IP 55

Physical specifications | Safety agency | CE compliant | Cabinet/Case Material | Plastic |

Hardware Aluminium U bracket

Grille Aluminium

Color White - RAL 9002, Black - RAL 9005

Technical Specifications Page 2 of 3



DM 41TWO-WAY COMPACT SPEAKER

Size

Height Width Depth Weight 197 mm / 7.76 inches 130 mm / 5.12 inches 115 mm / 4.53 inches 1.7 kg / 3.75 lbs

Technical Specifications Page 3 of 3