


# Product data sheet

Specifications



## Thorsman - cable tie - natural - 4.8 x 370 mm

IMT46248

 **Discontinued on:** Sep 30, 2023

 **Discontinued**

### Main

product range	Thorsman
product type	Cable tie
colour	Natural
quantity per package	Set of 100

### Complementary

Minimum tightening diameter	3.5 mm
Maximum tightening diameter	103.5 mm
Condition of use	Indoor
resistance to tearing	Resistance to tearing: 230 N
Material	PA (polyamide) 6.6 UV-stabilised
Length	370 mm
width	4.8 mm
Net weight	0.227 kg
Market segment	Small commercial

### Environment

Environmental characteristic	Fire resistance needle flame 30 s conforming to IEC 60695-11-5
Flame retardance	Self-extinguishing conforming to UL 94 V2
Ambient air temperature for operation	-40...85 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.1 cm
Package 1 Width	0.5 cm
Package 1 Length	37 cm
Package 1 Weight	2 g
Unit Type of Package 2	BAG
Number of Units in Package 2	100
Package 2 Height	3.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	14 cm
Package 2 Length	49 cm
Package 2 Weight	246 g
Unit Type of Package 3	CAR
Number of Units in Package 3	3500
Package 3 Height	40 cm
Package 3 Width	40 cm
Package 3 Length	12 cm
Package 3 Weight	9.106 kg

# Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[How this information helps you](#) >

## Environmental footprint

Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1
---	---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
--------------------------	---

## Use Better

### Materials and Substances

<a href="#">EU RoHS Directive</a>	Pro-active compliance (Product out of EU RoHS legal scope)
-----------------------------------	--

REACH Regulation	<a href="#">REACH Declaration</a>
------------------	-----------------------------------

China RoHS Regulation	<a href="#">China RoHS declaration</a>
-----------------------	--

## Use Again

### Repack and remanufacture

Circularity Profile	No need of specific recycling operations
---------------------	--

Image of product / Alternate images

Alternative

---

