

OMNITRONIC ED-60T Horn Driver

Weather-proof driver, 70/100 V or 16 ohms, 60 W RMS

Art. No.: 80710890

GTIN: 4026397303025



List price: 71.28 €

incl. 19% VAT.

Features:

- Power selector switch
- 35 mm mounting flange (3.5 cm/1 3/8")
- Suitable for outdoor use IP44

Package contents

- 1 x speaker, 1 x user manual

Logistic

EAN / GTIN: 4026397303025

Weight: 2,43 kg

Length: 0.13 m

Width: 0.12 m

Height: 0.19 m

Technical specifications:

IP classification:	IP44
Power:	Program: 120W Rated: 60W RMS
Frequency range:	350 - 5000 Hz
Sensitivity:	108 dB
Impedance:	Public address systems 100V; Public address systems 70V; 16 ohms
Power tapping:	7,5W; 15W; 30W; 60W RMS via no connector/cable only switchable
Speaker:	Horn vent 1,35"
Type of speaker:	Horn
Dimensions:	Height: 17,3 cm

Diameter: Ø 12,2 cm

Weight:

2,34 kg