

OMNITRONIC GCTH-815S Ceiling Panel 15W/pa

Drop-in ceiling speaker

Art. No.: 80710139

GTIN: 4026397349214



List price: 123.64 €

incl. 19% VAT.

Features:

- 2-way coaxial chassis with 20 cm woofer (8") and 4 cm silk dome tweeter (1.5")
- Easiest installation by simply resting the speaker on the ceiling grid
- Suitable for 60 x 60 cm grids - ceiling tile cutting necessary
- 4-step power selector
- Firedome for safety in case of fire
- Seismic safety points
- 2 pieces per set

Logistic

EAN / GTIN: 4026397349214

Weight: 9,80 kg

Length: 0.64 m

Width: 0.35 m

Height: 0.14 m

Technical specifications:

Output power:	10 W RMS (8 ohms)
Power:	Program: 30W Rated: 15W RMS
Frequency range:	55 - 18000 Hz
Sensitivity:	92 dB
Impedance:	Public address systems 100V; 8 ohms
Power tapping:	1,25W; 2,5W; 5W; 10W RMS via Selector switch switchable
Speaker:	Tweeter 1,5" Woofer 8"
Type of speaker:	Flush-mount speaker

Dimensions:	Width: 60,6 cm
	Depth: 11,5 cm
	Height: 31 cm
Weight:	9,20 kg