



MITCHELL & BROWN JB-32DVD1811ST

32" | HD READY | FREESAT | DVD COMBI | SMART TV



12V

NETFLIX

SMART TV



HDMI 



General

Model Number JB-32DVD1811ST
EAN TBC
Energy Rating E
Tuner Broadcasting DVB-T2/DVB-S2

Display

Screen Size 32"
Resolution Size 1366 x 768
Resolution Type HD Ready
Screen Type LED

Video

Dynamic Contrast Ratio 3000:1

Design

TV Colour Piano Black
Stand Type Central Stand
Stand Colour Piano Black

Smart Features

Audio Link (Bluetooth) No
WiFi Yes
Netflix Yes
Amazon Prime Video Yes
Youtube Yes

Audio

Support High Resolution Audio Yes
Headphone Socket Yes
Speakers 2 x 6W

DVD

CD Compatible Playback Yes
DVD Compatible Playback Yes
Multiple Language Options Yes
Skip Forward/Reverse Yes

Connectivity

HDMI 2
USB 2
Scart Input No
Digital Audio Out Yes

Power & Energy

Power Supply DC12V-5A / AC
100V-240V
Energy Efficiency Class E
Max Power Consumption 60 W
On-mode Power Consumption 25 W
Standby Power Consumption 0.5 W

Dimensions

Set Size without Stand (WxDxH)
730 x 94 x 430.7 mm
Set Size with Stand (WxDxH)
730 x 195.8 x 469 mm
Package Size (WxDxH)
811 x 125 x 500 mm
VESA Size M5 100 x 100 mm

Weight

Set Weight 5kg

Warranty

Warranty 7 Years