



# Big Digit Clock with Vibration Alarm Pad

SKU: 2300

Thank you for purchasing a Lifemax Big Digit Clock with Vibration Alarm Pad. Ideal for the hard of hearing, your clock offers an alarm with the choice of sound, vibration or both and is powered by battery or USB. Featuring large, clear white numbers on a black your clock displays the time, date and temperature and offers 3 alarm options with a strong vibration motor. To help you get many years of use from this product we recommend you read this document thoroughly to familiarise yourself with how your product works.

## Figure 1

- 1) ALARM
- 2) MODE
- 3) SNOOZE
- 4) UP/DOWN
- 5) VIBRATION PAD



## Operating Instructions

If you wish to use the vibration alarm, please insert the USB plug at the end of the vibration pad lead into the square USB socket on the rear of the Big Digit Clock. The vibration puck should be placed under your pillow taking care that the trailing lead is positioned so as not to pose any risk of entanglement or trip hazard.

Your Big Digit Clock can be powered by USB or 3 x AAA batteries. To power by USB attach the round connector on the lead provided to the round hole on the back of the unit. To power by batteries:

1. Locate the battery compartment cover on the rear of the unit and gently pull back on the tab securing the battery compartment cover in place to allow removal of the cover.
2. Insert three AAA batteries as indicated inside the compartment, observing the correct polarity (+/-).
3. Replace the battery compartment cover and close firmly. You will hear a click when the cover is secured.

When first switching on the LED display will fully illuminate for 2 seconds and a sound will be heard. The clock will then enter normal time mode displaying 0:00 in 24hr format. Pressing the MODE button will cycle through the clock functions:

TIME → DATE → TEMPERATURE → NIGHT MODE

## Setting the time

1. With the clock showing the the time, press and hold the MODE button for 3 seconds.
2. Choose between 12/24 hour clock modes by pressing UP and confirm by pressing MODE. In 12 hour mode, PM is displayed after midday.
3. Set the hour by pressing UP or DOWN, taking care when in 12 hour mode to correctly choose between AM and PM. Press MODE to confirm.
4. Set the minute by pressing UP or DOWN and confirm by pressing MODE.
5. The clock will exit the setting mode after completing step 4 or if left untouched for 10 seconds.

## Setting the date

1. Press MODE until the date is displayed (default 01/01/2018) and then press and hold MODE for 3 seconds.
2. Choose the year by pressing UP or DOWN and confirm by pressing MODE.
3. Set the month by pressing UP or DOWN and confirm by pressing MODE.
4. Set the day by pressing UP or DOWN and confirm by pressing MODE.
5. The clock will exit the setting mode after completing step 4 or if left untouched for 10 seconds.

## Alarm function

Press ALARM to display the current alarm time and press ALARM again to turn the alarm on or off. At the alarm time the alarm will gradually increase in volume over one minute. To snooze the alarm press SNOOZE or to stop the alarm press any other button.

The Big Digit Clock offers three alarm options, Sound Only (B1), Vibration Only (SH) and Sound and Vibration (BS). This is chosen when setting the alarm. When enabled, the alarm can be set with one of three repeat option, Daily (1-7), Monday to Saturday (1-6) or Weekdays Only (1-5). This is chosen when setting the alarm, as well as the snooze length of the alarm in minutes (default 5 minutes).

## Setting the alarm

1. Press and hold ALARM for 3 seconds to enter the setting mode.
2. Set the alarm hour by pressing UP or DOWN, taking care when in 12 hour mode to correctly choose between AM and PM. Press ALARM to confirm.
3. Set the alarm minute by pressing UP or DOWN and confirm by pressing ALARM.
4. Choose the alarm type by pressing UP or DOWN (Sound Only (B1), Vibration Only (SH) or Both (BS)) and confirm by pressing ALARM.
5. Set the snooze duration by pressing UP or DOWN (0 - 60 minutes) and confirm by pressing ALARM.
6. Set the repeat type by pressing UP or DOWN (Every Day (1-7), Mon - Sat (1-6) or Weekdays (1-5)) and confirm by pressing ALARM.
7. The clock will exit the setting mode after completing step 6 or if left untouched for 10 seconds.

## Temperature function

Press MODE twice to display the room temperature (in the range -10°C - 50°C). The temperature can be switched between °C and °F by pressing DOWN while the temperature is displayed. The clock can also be set to display the time, date and temperature in a continually cycle by holding MODE when the temperature is displayed. Hold MODE once mode to disable this option.

## Power saving function and night mode

The display is always on when the clock is powered by USB. To turn the display off, hold SNOOZE while the time is displayed. To turn the display back on, press any button. When powered by battery, the display will turn off after 16 seconds. Press any button to illuminate the display.

To adjust the brightness of the display, press UP repeatedly. The clock can be set to automatically reduce brightness during night time hours, as follows:

1. With the clock showing the the time, press MODE three times.
2. Toggle the night mode on or off using UP and DOWN or hold MODE for 3 seconds to enter setting mode.
3. Set the night mode start hour by pressing UP or DOWN, taking care when in 12 hour mode to correctly choose between AM and PM. Press MODE to confirm.
4. Set the night mode start minute by pressing UP or DOWN and confirm by pressing MODE.
5. Set the night mode end hour by pressing UP or DOWN, taking care when in 12 hour mode to correctly choose between AM and PM. Press MODE to confirm.
6. Set the night mode end minute by pressing UP or DOWN and confirm by pressing MODE.
7. The clock will exit the setting mode after completing step 6 or if left untouched for 10 seconds

### Warranty

In the unlikely event that your item develops a manufacturing fault, it is covered by a one year return to base warranty. Your warranty runs for 12 months from the date of purchase and is only valid with the original receipt, please ensure you keep this safe.

If your product develops a defect during the warranty period, please call the helpline number for further advice. If instructed, please securely pack your item and return enclosing your contact details, proof of purchase and fault details. We will, at our discretion, repair or exchange the item in line with warranty legislation. Where no proof of purchase is provided, or the product is outside the warranty period, repairs/replacements will be offered at cost to the customer.

Your warranty does not cover consumables, misuse or customer damage and will be deemed void where the repairs have been attempted by an unauthorised agent. This does not affect your statutory rights.

Please visit [www.lifemaxuk.co.uk/warranty](http://www.lifemaxuk.co.uk/warranty) to register.

### Battery Guide

1. Always remove batteries when the device is not in use.
2. Batteries should only be installed/replaced by an adult.
3. Use only 3 x AAA alkaline batteries. Do not mix alkaline and zinc carbon batteries.
4. Do not use rechargeable (nickel cadmium) or mercury oxide batteries.
5. Do not mix old and new batteries, replace all batteries together.
6. Read instructions and carefully install batteries observing the polarity (+/-) markings.
7. Remove exhausted batteries and dispose of safely.
8. Do not short circuit battery contacts.
9. Do not dispose of batteries in a fire.



Lifemax Limited, 1 Pipers Court,  
Thatcham, Berkshire, RG19 4ER

Lifemax (Ireland), 51 Bracken Road,  
Sandyford, Dublin, D18 CV48

[www.lifemaxuk.co.uk](http://www.lifemaxuk.co.uk)

