

Power Cord Cable Assembly

multicompPRO


**RoHS
Compliant**



Specifications

Connector to Connector	: Mains Plug, Denmark to IEC 60320 C13
Current Rating	: 10A
Voltage Rating	: 250V
Cable Length	: 2m
Jacket Colour	: Black

Diagram



No	Description	Qty
1	H05VV-F 0.75mm² 3C BLACK	1
2	Moulded Plug : LP-40 10A 250V	
3	Moulded Connector: LS-13G 10A 250V	
4	Mini Tie	
5	Label	

Notes

1. Cable : The Cord Shall Comply with IEC 60227 / EN 50525.
2. Plug : The Moulded Plug Shall Comply With DK/SB 107-2-01.
3. Connector : The Moulded Connector Shall Comply With IEC 60320-1 Standard (C13 Connector).
4. Colour : Black

Part Number Table

Description	Part Number
Mains Plug, Denmark to IEC 60320 C13, 2m, Black	GW-151852

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO