Part Number : 334723005
Product Description : MX150 Mat-Sealed Female Connector Assembly, Dual Row, 16 Circuits, Keying Option A, with Clipslot, with Connector Position Assurance, Black
Series Number : 33472
Status : Active
Product Category : Connector Housings
Engineering Number : CVP334723005



Documents & Resources

Drawings
334723005_sd.pdf

3D Models and Design Files
334723005_stp.zip

Specifications
AS-33611-001-001.pdf
PS-33472-000-001.pdf
TS-33472-0001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	33472
Description	MX150 Mat-Sealed Female Connector Assembly, Dual Row, 16 Circuits, Keying Option A, with Clipslot, with Connector Position Assurance, Black
Application	Power, Wire-to-Board, Wire-to-Wire, Automotive
Product Name	MX150
UPC	191128271417

Agency

UL	E29179

Physical

Circuits (maximum)	16
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	19.000/g
Number of Rows	2

Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +150°C

Use with Part(s)

Description	Part Number
MX150 Sealed Receptacle Cavity Plug	343454001
MX150 Female Terminals	33001
MX150 Female Terminals	33012