



Part Number : [1212080042](#)
Product Description : mPm DIN Valve Connector, Form B-11mm, External Thread, 2 Pole Plus Ground with A1 Circuit, 115V, Red LED, Transparent, Nitrile Gasket
Series Number : 121208
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : S22200TA140R




Documents & Resources

Drawings
[1212080042_sd.pdf](#)

Specifications
[PK-121208-S22-001.pdf](#)
[STR-1251-001.pdf](#)
[PS-121201-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	121208
Description	mPm DIN Valve Connector, Form B-11mm, External Thread, 2 Pole Plus Ground with A1 Circuit, 115V, Red LED, Transparent, Nitrile Gasket
IP Rating	IP65, IP67
Product Name	mPm
Type	Field Attachable Connector
UPC	884982509603

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	115V

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	Yes
Diagnostics Port	No
Form	B - 11mm
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Silver

Net Weight	19.489/g
Orientation	90° Angle
Pitch - Mating Interface	11.00mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size (AWG)	N/A