



# Product Data Sheet

## Folding Probe

Foldable thermometer with stainless steel sensor probe, adjustable from 0 to 180 degrees, to allow different angle viewing. Suitable for a variety of uses including HVAC, food processing, agriculture, laboratory and energy management.

The probe folds away conveniently for easy storage when not in use.

### Product Features

- Foldable probe for convenient use and easy storage
- Stainless steel probe adjusts from 0° to 180°
- Protection to IP 65
- One second temperature sensing time
- Auto power on when probe is opened more than 30° angle
- Auto power off when probe is closed less than 30° angle
- Wrist strap and battery included

### Product Specifications

<b>Temperature Range:</b>	-50 to +250°C/°F (switchable)
<b>Accuracy:</b>	±1°C between -20°C and +150°C, otherwise ±2°C
<b>Resolution:</b>	0.1°C
<b>Battery:</b>	LR44 x 1 pc
<b>CE:</b>	Approved
<b>ROHS/WEEE:</b>	Compliant
<b>Hazard Information (SDS):</b>	See <a href="http://www.brannan.co.uk">www.brannan.co.uk</a> for information
<b>LCD Dimensions:</b>	15mm x 32mm
<b>Probe Length:</b>	85mm
<b>Probe Diameter:</b>	3.5mm ø
<b>Product Dimensions:</b>	45mm x 125mm x 18mm (with probe closed)
<b>Product Weight:</b>	Gross - 85g Net - 50g (incl. battery & wrist strap)
<b>Display Card Weight:</b>	5g
<b>Display Card Dimensions:</b>	171mm x 130mm
<b>Display PVC Blister Weight:</b>	30g
<b>Display PVC Blister Dimensions:</b>	209mm x 145mm x 25mm



Auto switch off when probe is closed to less than 30° angle.



Description	Barcode	Product No
Folding Probe Thermometer	5 011405 311757	31/175/0