

Finity, Stretch Vinyl based Synthetic Polymer Disposable Glove



- **Range** Finity - Powdered synthetic disposable glove (PFT100)
- Finity PF - Powder free synthetic disposable glove (FT100)
- Finity PF30 - Powder free synthetic disposable glove 30cm long (FT130)
- **Latex Free** Ideal for those who are sensitised to Latex
- **Sensitive** A thin powder free synthetic glove with an excellent fit that feels like a second skin
- **Strong** Although it is a disposable glove, it is strong enough to be re-used
- **Ambidextrous** Fits either hand
- **Comfort** The soft formulation provides greater comfort and is more flexible and dextrous to wear

Description	5.5	6.5	7.5	8.5	9.5	Length
Finity PF30	FT130/00	FT130/01	FT130/02	FT130/03	FT130/04	30cm
Finity PF		FT100/01	FT100/02	FT100/03	FT100/04	24cm
Finity		PFT100/01	PFT100/02	PFT100/03	PFT100/04	24cm

Thickness: 0.08mm (Single Wall measured at palm)
Fit for special purpose

Typical Handling Applications

- Pharmaceutical
- Electronics
- Local Authorities
- Hospitals & Clinics
- Inspection
- Laboratory
- Emergency Services
- Food Processing



EN455 Medical
Devices Class I

Except Fatty Foods

[Symbols explained](#)

Advanced hand protection from Polycy - "Leading the European Glove Market in Innovation, Quality and Service"

© BM Polycy Limited, 2008 - Registered in England No. 1368212

[Recycle More](#)