



Charge 'n' Drive

Magnetic Wireless Car Charger



Charging for Every Journey

The Charge 'n' Drive "Ice Cooling" Magnetic Wireless Car Charger delivers up to 15W for Qi-compatible Android devices and 7.5W for iPhones, ensuring reliable charging on the go.

Its RGB backlight adds style and enhances nighttime usability, creating a vibrant glow on your dashboard for an improved driving experience.

The advanced ice-cooling system, featuring a smart fan and semiconductor chilling plate, prevents overheating, allowing uninterrupted, efficient charging even on long or hot drives.

Flexible mounting options include ventilation, dashboard, and windscreen setups, with 360° rotation for ideal viewing angles during navigation, calls, or music control.

Safety features include protection against over-current, over-voltage, short circuits, overheating, and foreign object detection.



15W max for
iPhone/Android



Magnetic
Wireless Charging



Active
Cooling



Qi
Charging

[verbatim.com](https://www.verbatim.com)



General Information

Approx. product dimensions LxWxH	60 x 95 x 42.3 mm
Product weight	112 g
Product material	Glass, ABS+PC
Colour	Black
Opening/Closing system	Automatic
Mounting options	3: Air vent, on dash board or windscreen
Phone width min to max	there is no limit of the phone size as it doesn't come with a grip
Phone case thickness max.	3 mm
Charger compatibility	Qi-compatible smartphone

Power

Input (requirements for adapter)	DC 5V/3A, 9V/3A
Working frequency	110-360KHz
Charging distance	3 mm
Output	up to 15W for Qi-compatible Android devices and 7.5W for iPhones (requires a car charger provides power 30W or above and supports Quick Charge 3.0 or above , sold separately)
Charging Techonology	Qi1
Charging efficiency	≤70%
Cable	USB-C to USB-C
Cable Length	1 m

Other Features

Rotatable	Yes, 360°
Anti-slip	Yes
Light Indicators	Yes
Anti-scratch	Yes



Charging Pad



Car vent clip



Dashboard stand

Safety

Output short circuit protect	Yes
Over-voltage protection	Yes
Over-current protection	Yes
Over-temperature protection	Yes

Directives

Electromagnetic compatibility	2014/30/EC
Low voltage protection	2014/35/EC
General product safety	2001/95/EC
RoHS directive	2011/65/EC
Annex II	2015/863/EC
Test standards	EN 55032:2015+A11:2020+A1:2020 EN 55035:2017+A11:2020 EN 61000-3-2:2019+A2:2021 EN 61000-3-3:2013+A1:2019+A2:2021 EN IEC 62386-1:2020+A11:2020

Storage and Operating Conditions

Storage temperature	-10 °C to 60 °C
Operating temperature	0 °C to 40 °C
Operating humidity	5%(0°)~90%(40°)RH

PN	Description	Tariff Code	Bar Code	EAN128 Code	EAN14 Code
31862	Verbatim Charge 'n' Drive Magnetic Wireless Car Charger	85044095	023942318620	(02)00023942318620(37)05(91)845 (02)00023942318620(37)20(91)845	20023942318624 50023942318625

Logistic Information

Product Dimensions L x W x H	64.3 x 64.3 x 43.2mm (Charging pad)
Product Weight	105g (charging pad), 102g (Dashboard stand), 21g (car vent clip) (approx)
Units per Pack	1
Pack Dimensions L x W x H	106 x 67 x 146mm
Pack Weight	321 grams (approx)
Units per Inner Carton	5
Inner Carton Dimensions L x W x H	355 x 115 x 160mm
Inner Carton Weight	140 grams (approx)
Units per Outer Carton	20
Outer Carton Dimensions L x W x H	370 x 245 x 345mm
Outer Cartons Weight	7608 grams (approx)
Outer Cartons per Layer	75
Layers per Pallet	5
Units per Pallet	1500

Pack Contents

- Verbatim GaN Charger
- Dashborad stand
- Car vent clip
- USB-C to USB-C Cable
- Metallic ring
- Quick Start Guide



Warranty

2 year limited warranty

For more information, please
contact your key account manager



Publication date: 26/11/2024
© 2024 Verbatim. All rights reserved.
All brand names are registered trademarks of their respective owners.
Unauthorized use strictly prohibited.
Specifications are subject to change without prior notice.

