



Home : Connectors : N : EZ-240-NMH-RA-X

EZ-240-NMH-RA-X

Type N, male (plug), right angle, EZ style connector for LMR[®]-240 and TCOM[®]-240 type cables. The EZ-240-NMH-RA-X eliminates assembly errors and soldering with crimp-style outer contacts and spring finger inner contacts. It features a no-braid trim design, eliminating FOD and guaranteeing an optimal and consistent termination. The BeCu pins are designed to maximize surface contact and minimize current density. They provide a strong spring force making the EZ connectors a perfect choice for extreme cold and high- vibration

applications where the center conductor might contract. The Type N is a durable, weatherproof, medium-size RF connector designed for systems where excellent RF and mechanical performance is critical. They feature a threaded coupling mechanism and are fully interchangeable with N-Type connectors made to the MIL-C-39012 specification.



Stock Code: **3190-6143**

N-male (plug)



Specs



Compatible
with



Hardware



CAD Model



Documentation



Ask an Expert

Specifications

Part Number	EZ-240-NMH-RA-X
Stock Code	3190-6143
Interface	N
Gender	Male (plug)
Orientation	Right Angle
PIM Rating	N/A
Impedance (ohms)	50

Max Frequency (GHz)	6
VSWR Freq	<1.30:1
VSWR Frequency (GHz)	6
Coupling Nut	Hex/Knurl
Inner Contact Attach	Spring Finger
Outer Contact Attach	Crimp
Body Finish	Alballoy

Pin Finish	Gold
Length (mm)	25.1
Length (in)	1
Width (mm)	26.4
Width (in)	1.04
Weight (g)	52
Weight (lb)	0.11