

Technical data sheet

Article number:
151-04463

MAGRB5

Product Group	Mounts with cable clip, magnetic
Product Family	MAGRB-Series
Material	Polyamide 6.6 (PA66), Neodymium alloy R5 (NDFEBR5)
Colour	Black (BK)
Bundle Ø max.	5.0 mm
CE Certification	No
Fixation Method	Magnet
Flammability	UL 94 V2 (excluding adhesive)
Height (H)	6.0 mm
Length (L)	19.0 mm
Operating Temperature	-40 °C to +85 °C
Package Content packed in	bag
Pack Cont.	25 pcs.
UV-resistant acc. to ASTM D6779 (Yes/No)	No
Variant	Clip
Width (W)	19.0 mm

