



BoomTone DJ - BOOMMaster 300



Active Loudspeaker

BoomTone DJ BOOMMaster 300 portable battery-powered speaker. Equipped with two 6.5" speakers, a carrying handle and numerous inputs (Bluetooth, USB, microphone and line), this portable speaker can be taken anywhere.



- BoomTone DJ BOOMMaster 300
- Portable PA speaker
- Karaoke speaker
- Woofer: 2x 6.5" / 16 cm
- Tweeter: 2" tweeter
- Max. power: Peak: 250 W
- Bandwidth: 55 Hz - 18 kHz
- USB / SD reader
- Tuner mode
- Built-in light
- Bluetooth: TWS Version 5.0

- Bluetooth range: 10 meters
- Battery: 3.7 V / 3600 mAh lithium battery
- Battery life: 2 to 4 hours
- Battery charging time: 3 to 4 hours
- 5 V USB-C charging (adapter not included)
- IR remote control
- Net weight: 3.75 kg
- Gross weight: 4 kg
- Product dimensions: 220 x 240 x 500 mm

• EAN : 3700752715487

- Weight : 4.8Kg
- Package Dimensions : 287x262x635mm
- Product Dimensions : 240x220x500mm

