

KEW80L

Mobile bluetooth printer



PRODUCT DATA SHEET

KEW80L

MOBILE BLUETOOTH PRINTER

- Easy to use mobile printer
- Adjustable paper / label roll width up to 58mm
- 50mm print roll diameter
- Works with the KEWPAT APP for printing PAT testing labels
 - Generic PASS / FAIL
 - Your bespoke PASS / FAIL
 - QR codes
 - Barcodes
- Comes with a roll of polypropylene 39mm x 25mm labels (250 approx.)
- Bluetooth and USB interface
- 1200mA / 7V rechargeable battery



SPECIFICATIONS

Printing Method	Thermal Transfer
Paper roll / label width	58mm (max)
Print Speed	50 - 90mm/s
Max roll diameter	50mm
Resolution	203dpi
Input buffer	256K
Power adaptor output	9V 1A
Charging time	4 hrs (can print whilst charging)
Battery	Lithium 1200mAh / 7V
Operating temperature range	0°C ~50°C
Operating humidity	20%~85% RH
Storage temperature range	-20°C~60°C
Storage humidity range	5%~95% RH
Mechanical life	50Km
Dimensions (mm)	85(w) x 60(h) x 115(d)
Weight	275g approx. (without print roll)

ACCESSORIES

- 1 x label roll
- Battery pack
- Power adaptor
- Instructions

OPTIONAL

KEW80 Label – Label rolls (2 rolls)