

Description

MG Chemicals brushes enhance the delivery of chemical cleaners and remove loose debris that cleaners alone cannot. The bristles come in stainless steel, brass, horse, or hog hair. The brush handles come in a selection of wood, stainless steel, cad plated steel, or tin. Depending on the application, the brushes offer abrasive, non-abrasive, or anti-static properties.




Features

- **Anti-static**—Cat No. 852, 853, 855, 856, 857, and 859
- **Easy grip handles**

Bristle Materials






<i>Stainless Steel</i>	Highly abrasive bristles that are resistant to heat, rust, and corrosion
<i>Brass</i>	Abrasive and flexible bristles that are good for soft metal surfaces
<i>Hog Hair</i>	Fairly stiff hair, non-abrasive bristles with excellent durability, and water resistance. Heat tolerant to 188 °C [370 °F].
<i>Horse Hair</i>	Durable, soft to slightly stiff bristles that can be used for scratch-free dry brushing and polishing. It is not resistant to acids or alkalis. Heat tolerant to 188 °C [370 °F].

Product Details

<i>Cat No.</i>	<i>Trim</i>	<i>Rows</i>	<i>Brush Face (L x W)</i>	<i>Handle (L x W)</i>	<i>Handle Material</i>	<i>Quantity</i>
Stainless Steel Cleaning Brush						
 850	7/16"	3 x 7	1 3/8" x 1/4"	7 3/4" x 7/16"	Plywood	1
Brass Cleaning Brush						
 851	7/16"	3 x 7	1 3/8" x 1/4"	7 3/4" x 7/16"	Plywood	1
Hog Hair Cleaning Brush						
 852	7/16"	3 x 7	1 3/8" x 1/4"	7 3/4" x 7/16"	Plywood	1

Brushes Technical Data Sheet

850 851 852 853 855 856 857 859

<i>Cat No.</i>	<i>Trim</i>	<i>Rows</i>	<i>Brush Face (L x W)</i>	<i>Handle (L x W)</i>	<i>Handle Material</i>	<i>Quantity</i>
Large Hog Hair Cleaning Brush						
 853	3/4"	4 x 9	2-1/8" x 7/8"	8 1/4" x 1 1/16"	Plywood	1
Horse Hair Cleaning Brush						
 855-5	3/4"	—	1/2" (W)	5 1/4" x 3/8"	Tin	1
855-144	3/4"	—	1/2" (W)	5 1/4" x 3/8"	Tin	1
Double Horse Hair Cleaning Brush						
 856	1/4"	—	1/2"	4 1/2" (L)	Stainless steel	1
Chisel Hog Hair Cleaning Brush						
 857	1/2"	2 x 6	7/8" x 3/8"	4 15/16" x 1 1/16"	Plywood	1
Horse Hair Cleaning Brush						
 859	7/16"	3 x 7	1 3/8" x 1/4"	7 3/4" x 7/16"	Plywood	1

Note: All dimensions are an approximation.



ISO 9001 Registered Quality System.
Burlington, Ontario, Canada QMI File # 004008

Brushes Technical Data Sheet

850 851 852 853 855 856 857 859

Technical Support

Contact us regarding any questions, improvement suggestions, or problems with this product. Application notes, instructions, and FAQs are located at www.mgchemicals.com.

Email: support@mgchemicals.com

Phone: +(1) 800-340-0772 (Canada, Mexico & USA)

+(1) 905-331-1396 (International)

Fax: +(1) 905-331-2862 or +(1) 800-340-0773

Mailing address: **Manufacturing & Support**
1210 Corporate Drive
Burlington, Ontario, Canada
L7L 5R6

Head Office
9347-193rd Street
Surrey, British Columbia, Canada
V4N 4E7

Warranty

M.G. Chemicals Ltd. warrants this product for 12 months from the date of purchase by the end user. *M.G. Chemicals Ltd.* makes no claims as to shelf life of this product for the warranty. The liability of *M.G. Chemicals Ltd.* whether based on its warranty, contracts, or otherwise shall in no case include incidental or consequential damage.

Disclaimer

This information is believed to be accurate. It is intended for professional end users having the skills to evaluate and use the data properly. *M.G. Chemicals Ltd.* does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.