

19" Rack Mount DIN Rail Panel



19" Recessed Rack Mount DIN Rail Panel (FFDIN)

This rack mount 1U panel is designed for mounting DIN rail connectors. The TS35 rail is recessed by 90 mm and the frame is equipped with cable tie and access features to accommodate most equipment and connectors.

Features

- 1U panel fitted with TS35 DIN rail
- 90mm recess with cable access points at both sides
- Supplied with convenient rear cable tie facilities
- Provided with M6 mounting kit of 4 caged nuts, bolts and washers
- Zinc-coated steel unpainted DIN rail ensures optimal earthing

Specifications

- Weight: 669g (including primary packaging)
- Dimensions: 512x109x55mm (in primary packaging)
- Colour: black
- Frame: Carbon steel
- DIN rail: Chromated zinc-plated mild steel

Packaging: Packed in a white card box then in cartons of 10

EAN: 5055386513229

Commodity Code: 85444920

Country of Origin: China



Illustrative image

ROHS Compliant

Code: FFDIN

