



**MADE IN  
GERMANY**



**Product number** 1153690400  
**EAN** 4007123654499

### DESCRIPTION

- Stackable, splash-proof housing made from a special rubber compound for continuous load.
- Extremely robust, impact resistant, ageing and weather resistant.
- Resistant to a variety of oils, greases, gasoline and acids, UV and ozone radiation.
- Housing resistant to temperatures from -30 °C to +80 °C.
- Quality sockets in accordance with VDE 0620-1.
- Certified circuit breakers for your safety.
- Sturdy metal carrying handle.
- Oil resistant rubber cable for permanent outside use.
- Earthed sockets 230 V in pairs with different phases.

### TECHNICAL DATA

Cable quality	Rubber-Neoprene	CEE 400 V / 16 A / 3P+N+PE (5p) Steckdosen	2
Cable length	2 m	CEE 400 V / 32 A / 3P+N+PE (5p) Steckdosen	1
Cable designation	H07RN-F 5G4,0	Earthed socket outlets	4
Cable colour	black	Plug system socket	Type F (Protective contact)
Max. current carrying capacity	32 A	Supply/ connection option	Supply cable with plug
Miniature circuit breaker	4	Plug system plug	CEE 32 A 3P+N+E (5p) 400 V
Residual current circuit breaker (RCCB)	Without	Degree of protection (IP)	IP44

### PACKAGING, DIMENSIONS AND WEIGHTS

Packaging	Neutral carton	Dimension LxWxH (without packing)	26.5 cm x 34 cm x 23 cm
UP	1	Weight of product (including packaging)	4.36 kg
Weight of product (without packaging)	4.35 kg	Dimension LxWxH (incl. packing)	26.5 cm x 34 cm x 23 cm

### SCOPE OF DELIVERY

Compact power distributor BSV 3/32 2 IP44