

UB402MP BLOWER ATTACHMENT

1912R8-4

UB402MP BLOWER ATTACHMENT

For use with UX01G, DUX60 & DUX18



Technical specifications

Product Dimensions (L x W x H):	660 - 760 x 136 x 139 mm
No load speed with DUX18	0 - 6700 / 9600 min ⁻¹
No load speed with DUX60	0 - 5700 / 8100 / 9600 min ⁻¹
No load speed with UX01G	0 - 5700 / 8100 / 9600 min ⁻¹
Air volume with DUX18	0 - 4,3 / 6,2 m ³ /min
Air volume with DUX60	0 - 3,6 / 5,3 / 6,2 m ³ /min
Air volume with UX01G	0 - 3,6 / 5,3 / 6,2 m ³ /min
Max air speed with DUX18	33,4 / 47,4 m ³ /min
Max air speed with DUX60	28,0 / 40,3 / 47,4 m ³ /min
Max air speed with UX01G	28,0 / 40,3 / 47,4 m ³ /min
Average air speed with DUX18	0 - 27,3 / 39,1 m/s

EAN 0088381127165

Link to product - www.makita.uk.com

