

PHILIPS



Wireless speaker

IP67 dust/water protection

Bold bass

Built-in mic for calls

Up to 12 hours of music



TAS4807W

Go move! The small speaker with bold sound.

Surf. Run. Dance. Box. Whatever gets you moving, this waterproof speaker with a funky two-tone design goes with you. You get bold sound despite the compact size, and a lanyard strap that makes the speaker easy to carry. Let's go!

Go move!

- Small speaker. Bold sound
- Dual passive radiators. Punchy bass
- 12 hours play time. Keep the tunes going
- IP67 dustproof and waterproof. Ready to rock*

Love the convenience

- Bluetooth multipoint. Connect multiple devices
- Hands-free calls. Push-to-talk voice-assistant activation
- Easy control for music and more

Love where you go

- Detachable lanyard. Take the speaker anywhere
- Dimensions: 170 x 72 x 70 mm
- Pair for stereo. Go bigger

Highlights

Small speaker. Bold sound



From parks to campsites—bring the music you love wherever you go! This portable speaker gives you clear sound and the bass is big and bold thanks to dual passive radiators. Want to rock even harder? Pair two speakers for party-starting stereo.

12 hours play time



Cranking up the tunes? This speaker can keep going as long as you can. You get up to 12 hours of play time from a fully charged speaker. More than enough for a workout or a party around the campsite fire.

IP67 dust/water protection



From the trail to the beach to the pool—an IP67 rating ensures this speaker can go anywhere. The detachable lanyard makes carrying easy and a

Bluetooth range of up to 20 m means you won't miss a beat. Even if your phone is a long way from the speaker.

Bluetooth multipoint

Mix and match your workout playlists! With Bluetooth multipoint connectivity, you can connect up to two smart devices to this speaker simultaneously—and take turns pumping up the tunes. If a call comes in, the built-in mic lets you take it without disconnecting your phone from the speaker.

Easy control

Buttons on the speaker's outer case let you control volume, music playback, stereo pairing and Bluetooth. Want to tell your phone to play a certain song? Press and hold the play/pause button to talk to your voice assistant.

Hands-free calls



Hands-free calls. Push-to-talk voice-assistant activation

Specifications

Sound

Output power (RMS): 10 W
Sound System: Mono
Frequency response: 80 Hz - 20 KHz
Output power (MAX): 20 W

Loudspeakers

Full-range driver diameter: 45 mm
Number of full-range drivers: 1
Driver configuration: Full range
Number of sound channels: 1
Passive radiators: 2

Connectivity

Bluetooth: support SBC streaming
Microphone: Built-in microphone
Type of cable: USB cable (Type-C)
Bluetooth version: 5.2
Bluetooth profiles: A2DP, AVRCP, Multipoint (Multipair) support
Bluetooth range: Line of sight, 20 m or 66 ft
DLNA Standard: No
Multiple speaker connection
Multiple speaker scenario: Stereo
Multiple speaker technology: TWS

Convenience

Automatic power off
Ease of Installation: Automatic pairing
Call Management: Answer/End Call
Volume control: Digital up/down
Water resistance: IP67
Built-in microphone
Light Effect: No
Dustproof
Display screen: No
Hands-free calling

Compatibility

Smartphone/tablet APP control: No

Power

Battery Capacity: 3.7 V, 4400 mAh
Battery type: Lithium-ion (built-in)
Input: 5 V, 2 A
Operating time on battery: 12 hour(s)
Charging time: 3 hour(s)
Power bank: No

Packaging dimensions

Height: 14 cm
Packaging type: Box
Width: 20.5 cm

Depth: 9.8 cm
Number of products included: 1
EAN: 48 95229 12198 0
Gross weight: 0.74 kg
Net weight: 0.492 kg
Tare weight: 0.248 kg

Product dimensions

Height: 7 cm
Width: 17 cm
Depth: 7.2 cm
Weight: 0.492 kg

Accessories

Included accessories: carrying strap, Quick install guide, World Wide Warranty leaflet
Cable: USB charging cable

Design

Colour: White

UPC

UPC: 8 40063 20227 6

