

Hama Indoor/Outdoor Thermometer, 18 cm, Analogue

Thermometer



00186402

- Analogue thermometer for indoor and outdoor use
- Weatherproof plastic housing
- Also ideal for heating cost control or reduction: one degree less can save up to 6% on heating costs
- Eyelet for hanging on the wall with a nail or similar
- Clear scaling accurate to one degree
- Temperature display in degrees Celsius

Design (Colour, Pattern, Motif, Series)

Colour	White
Shade of colour	White

Physical Properties

Display	Analogue
Display	Analogue
Material	Plastic Material
Measurement Range (inside)	-30°C to +50°C
Measurement Range (outside)	-30°C to +50°C
Measuring Range	-30 C° up to +50 C°
Mounting	Hanging
Operating Mode	Manual
Special Feature	Weatherproof
Temperature Accuracy (Indoor and ±1°C Outdoor)	
Temperature Range	-30 C° up to +50 C° °
Temperature Resolution	1 °
Type	Indoor/outdoor thermometer

Size & Weight

Width x Depth x Height	2.6 x 0.9 x 18 cm
------------------------	-------------------