

Cisco SFP-GE-T Compatible SFP Module - 1000BASE-T - SFP to RJ45 Cat6/Cat5e - 10/100/1000 Mbps - RJ-45 100m - Cisco IE3400, IE3300, IE3200

**Product ID:** SFPC1110



The SFPC1110 is a Cisco SFP-GE-T compatible copper transceiver module that has been designed, programmed and tested to work with Cisco brand switches and routers. It delivers dependable 1GbE (1000 Mbps) connectivity over copper cable, for 1000BASE-T compliant networks, with a maximum distance of up to 100 m (328 ft).

Technical Specifications:

- Maximum Data Transfer Rate: 1.25 Gbps
- Type: Copper
- Connection Type: RJ45 Connector
- Maximum Transfer Distance: 100 m (328 ft)
- MTBF: 4,655,371 hours
- Power Consumption: Less than 1.3 Watts
- Digital Diagnostics Monitoring (DDM): No

This SFP copper module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility



## Applications

- Replacing defective or damaged SFP modules in Cisco switches and routers
- Expand your network to remote segments

## Features

- **100% CISCO SFP-GE-T COMPATIBLE:** Works with Cisco switches like IE3400, IE3300, IE3200, , and others
- **TECHNICAL SPECS:** 1000BASE-T 1 Gbps Copper RJ-45 Connector Distances up to 100m (328ft)
- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in Cisco routers and switches
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this SFP module is backed for life (lifetime of module, not network switch), including free lifetime 24/5 multi-lingual technical assistance.

---

### Hardware

Warranty	Lifetime
Compatible Brand	Cisco
Industry Standards	IEEE 802.3ab 1000BASE-T

---

### Performance

Maximum Data Transfer Rate	1.25 Gbps
Max Transfer Distance	100m [328ft]
Type	Copper
DDM	No
Compatible Networks	10/100/1000 Mbps
General Specifications	Compatible Network Note: 10/100/1000 Mbps (Requires equipment with SGMII capability)
MTBF	4,655,371 hours

	Power Consumption (In Watts)	< 1.3 W
<hr/>		
<b>Connector(s)</b>		
	Local Unit Connectors	1 - RJ-45
<hr/>		
<b>Power</b>		
	Output Voltage	3.3V DC
<hr/>		
<b>Environmental</b>		
	Operating Temperature	0C to 70C (32F to 158F)
	Storage Temperature	-40C to 85C (-40F to 85F)
	Humidity	30~70% RH
<hr/>		
<b>Physical Characteristics</b>		
	Product Length	2.8 in [70.0 mm]
	Product Width	0.5 in [1.3 cm]
	Product Height	0.5 in [1.3 cm]
	Weight of Product	1.6 oz [46.0 g]
<hr/>		
<b>Packaging Information</b>		
	Package Length	4.4 in [11.3 cm]
	Package Width	3.6 in [9.1 cm]
	Package Height	1.3 in [3.3 cm]
	Shipping (Package) Weight	1.7 oz [48.0 g]
<hr/>		
<b>What's in the Box</b>		
	Included in Package	1 - 10/100/1000 Mbps RJ45 SFP
<hr/>		

*\*Product appearance and specifications are subject to change without notice.*