

Technical Data Sheet

1. Name of cable: Speaker Cable
2. P/N: CB25443
3. Designed of cable:
 - 3.1 Inner conductor: 50/0.254±0.005mm Stranded Bare Copper
 - 3.2 Insulation: LSZH
 - 3.3 Size of Insulation: Ø2.9±0.1mm
 - 3.4 Core Color: Blue/Red
 - 3.5 Two Wires Stranded to a qual:
 - 3.6 Rip wire:
4. Jacket: LSZH
 - 4.1 Color: White
 - 4.2 Size: Ø7.0±0.3mm
 - 4.3 Wall thickness: ≈0.60mm
 - 4.4 Printing: By request bargain
5. Electric data at 20°C:
 - 5.1 Conductor resistance: ≤7.98Ω/km
 - 5.2 Testing voltage: wire/wire 50Hz 5min=2.5KV
 - 5.3 Elongation: ≥125%
 - 5.4 Tensile strength: ≥10.0Mpa
6. Other requirement:
 - 6.1 Permissible temperature: -20°C---60°C
 - 6.2 Packing: 100M On a non-returnable reel
 - 6.3 Test standard: This Technical Data Sheet