

## Technical Data Sheet

1. Name of cable:	Speaker Cable
2. P/N:	CB25445
3. Designed of cable:	
3.1 Inner conductor:	30/0.254±0.005mm Stranded Bare Copper
3.2 Insulation:	LSZH
3.3 Size of Insulation:	Ø2.4±0.1mm
3.4 Core Color:	Blue/Red
3.5 Two Wires Stranded to a qual:	
3.6 Rip wire:	
4. Jacket:	LSZH
4.1Color:	Black
4.2 Size:	Ø6.0±0.3mm
4.3 Wall thickness:	≈0.60mm
4.4 Printing:	By request bargain
5. Electric data at 20°C:	
5.1 Conductor resistance:	≤13.3Ω/km
5.2 Testing voltage:	wire/wire 50Hz 5min=2.5KV
5.3 Elongation:	≥125%
5.4 Tensile strength:	≥10.0Mpa
6. Other requirement:	
6.1 Permissible temperature:	-20°C---60°C
6.2 Packing:	100M On a non-returnable reel
6.3 Test standard:	This Technical Data Sheet