


|                               |      |      |
|-------------------------------|------|------|
| REVISION RECORD MODIFICATIONS | DATE | REV. |
| NEW                           |      | A/0  |



PIN OUT

| CN1 (568B)     |  | CN2 (568B)     |
|----------------|--|----------------|
| WHITE/ORANGE 1 |  | 1 WHITE/ORANGE |
| ORANGE 2       |  | 2 ORANGE       |
| WHITE/GREEN 3  |  | 3 WHITE/GREEN  |
| GREEN 6        |  | 6 GREEN        |
| BLUE 4         |  | 4 BLUE         |
| WHITE/BLUE 5   |  | 5 WHITE/BLUE   |
| WHITE/BROWN 7  |  | 7 WHITE/BROWN  |
| BROWN 8        |  | 8 BROWN        |

NOTE:

- Electrical test:
  - 100% open short & miss wire test;
  - Insulation resistance:DC 300V 3M $\Omega$ ;
  - Contactor resistance:3 $\Omega$ ;
- RoHS compliant
- MARKING:RW System Cable UTP CAT 6 4 Pairs 24AWG  
Stranded ISO 11801 250MHZ

MATERIAL LIST:

|     |            |                                                           |       |        | DRAW NO. | PRODUCT NAME | CAT. 6 UTP 8P8C - 8P8C |               |                |
|-----|------------|-----------------------------------------------------------|-------|--------|----------|--------------|------------------------|---------------|----------------|
| ③   | CABLE      | Cat. 6 7/0.18BC*4P UTP JACKET:PVC/BLACKOD:5.8 $\pm$ 0.2mm | 1     |        | CUSTOMER |              | VIEW                   | Tolerance     |                |
| ②   | PVC        | 75A PVC, COLOR: BLACK                                     | 2     |        | ITEM NO. |              |                        | X. $\pm$ 1.00 | X.X $\pm$ 0.50 |
| ①   | 8P8C PLUG  | RJ45 8P8C PLUG, CAT. 6 UTP Pin GOLD FU", Circle Type.     | 2     |        | APPOBY   | CHECKBY      | DRAWNBY                | UNTT          | MM             |
| NO. | PARTS NAME | SPECIFICATION DESCRIPTION                                 | QT' Y | REMARK |          |              |                        | Page          | 1 of 1         |