




NOTES:

1. MATERIAL

- 1.1 HDMI CABLE: [7/0.12BCx2C+7/0.12BCx1C+AM]x4PCS+
[7/0.10BCx7C+D(7/0.12BC)+AM]+BLACK PVC JACKET;
OD:3x13±0.2MM
CABLE MARKING:HIGH SPEED HDMI® CABLE
- 1.2 HDMI 19PIN TYPE A MALE:BLACK INSULATION,
GOLD PLATED CONTACTS ,GOLD PLATED SHELL.
- 1.3 ALL HOOD:MOLDED BLACK PVC.


2. ELECTRICAL

- 2.1 100% OPEN AND SHORT TEST.
- 2.2 CONDUCTOR RESISTANCE: 8 OHMS MAX.
- 2.3 INSULATION RESISTANCE: 10 MEGOHMS MIN.
- 2.4 HDTV-DVD TEST:1080P.

3. PACKAGING: A PC/PE-BAG.

4. ALL MATERIALS ARE REACH COMPLIANT.

CUSTOMER NO.	L
26755	1000±30mm
26757	7000±150mm
26741	10000±150mm
26756	3000±70mm
26739	2000±50mm



LENGTH TOLERANCE: X. ± 0.5 .X ± 0.2 .XX ± 0.1	SCALE: FREE	CUS. NAME:			ENG:
ANGLE TOLERANCE: X' ±3' .X' ±1'	UNIT: mm		PRODUCT NO:	CUSTOMER NO:	CHECKED:
	VERSION: 00		DRAWING NO: DS200804	PRODUCT DESCRIPTION: HDMI AM-HDMI AM/GOLD-PLATED	APPROVED:

00	NEW ISSUE	2020-08-04
REV.	MODIFY DESCRIPTION	DATE