

Planer XGT®

KP001GZ03

40Vmax • 82 mm



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	15000 min ⁻¹
Planing Width	82 mm
Chip Thickness (Planing Depth)	0 - 4 mm
Max. Shiplapping Depth	25 mm
AWS ready	✓
Sound Power Level (L _{WA})	98 dB(A)
Sound Pressure Level (L _{pA})	90 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Planing Softwood	4,3 m/s ²
Vibration Uncertainty (K Factor), Planing Softwood	1,5 m/s ²
Product net weight	2,5 kg

User benefits

- The rubber coating on the handle ensures a firm working grip
- Battery protection system automatically shuts off power when the battery level is low
- The front of the base has 3 grooves for making chamfers.
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Brushless motor is electronically controlled to optimise battery energy use for longer run time per charge
- Chip ejection can be directed to either side of the tool

EAN 0197050001412

Link to product - www.makitauk.com



Related products

Standard AC

122785-9
Guide Rule



442198-1
Anti Corrosion Paper

782209-3
Socket Wrench 9



821551-8
Makpac case (3)



8354R2-5
Inner Tray Type 3



Optional AC

122695-0
Blade Gauge Assembly 82 Mm



122785-9
Guide Rule



122793-0
Dust bag



191C19-9
Blade Gauge Assembly



191C22-0
Guide Assembly



251878-6
Screw M5X20

253807-5
Flat Washer 5, Ls0714



762001-3
Triangular Rule



782209-3
Socket Wrench 9



821551-8
Makpac case (3)



8354R2-5
Inner Tray Type 3



D-07945
TCT Mini Planer Blade, 82 mm



D-07967
Planer Blade T.C.T, 82 mm, 2 pcs



D-16346
Planer blade, HSS, 82 mm, 2 pcs



D-35302
Planer blade TCT, 82 mm, 10 pcs



Other

User manual

Parts drawing