

Rotary Hammer XGT®

HR003GZ01

40V max • SDS-Plus • 28 mm • 2,8 J

Powerful three-action hammer with vibration damping

Efficient combination hammer HR003G delivers high power for professional work. The tool is lightweight and the tool balance is redesigned for increased operability. HR003G is equipped with Anti vibration technology (AVT). The machine can also be connected to the DX12 dust extractor system. Tool only, battery and charger not included. Tool comes in a Makpac case



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 980 min ⁻¹
Impacts per Minute (IPM)	0 - 5000 min ⁻¹
Max. Drilling Diameter in Wood	32 mm
Max. Drilling Diameter in Concrete	28 mm
Max. Drilling Diameter in Steel	13 mm
Optimum Drilling Diameter Range in Concrete	6 - 20 mm
Impact Energy	2,8 J
Drilling diameter with TCT core bit	54 mm
Adapted for SDS-PLUS bits	✓
Electronic brake	✓
Sound Power Level (L _{WA})	103 dB(A)

User benefits

- Battery protection circuit protects against overloading, over-discharging and over-heating
- AVT (Anti-Vibration Technology) ensures extra-low vibration performance
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Low power consumption thanks to brushless motor
- 3-Mode operation for "Rotation Only", "Hammering with Rotation" or "Hammering Only" for multiple applications
- Constant speed control maintains constant speed under load

EAN 0088381893046

Link to product - www.makitauk.com



Related products

Standard AC

331886-4
Depth Gauge

443122-7
Cleaning Cloth

835E79-0
Inner tray (4)

194683-7
Grease vessel set, 100 ml

821552-6
Makpac case (4)



Optional AC

331886-4
Depth Gauge

835C84-5
Makpac Inner Tray Type 4

198993-4
Grease vessel for bit 100 ml

443122-7
Cleaning Cloth

194683-7
Grease vessel set, 100 ml

821552-6
Makpac case (4)

424474-5
Sealing Cap



Other

User manual

Parts drawing