

Reciprocating Saw XGT®

JR001GZ

40V max • 0 – 3 000 min⁻¹ • 32 mm

Efficient brushless reciprocating saw

An efficient brushless reciprocating saw for spark-free cutting of metal and demolition work for professional use. Two speed settings, stroke length of 32 mm and stroke rate of 0 – 3 000 min⁻¹ with continuous control from the switch. Quick-release blade attachment. Tool only, battery and charger not included



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Strokes per Minute (SPM)	0 - 2300 / 3000 min ⁻¹
Length of Stroke	32 mm
Max. Cutting Capacity in Wood (90°)	255 mm
Max. Cutting Capacity in Steel Pipe	130 mm
Sound Power Level (L _{WA})	96 dB(A)
Sound Pressure Level (L _{pA})	85 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Cutting Boards	18,0 m/s ²
Vibration Uncertainty (K Factor), Cutting Boards	1,5 m/s ²
Vibration Level, Cutting Wooden Beam	19,5 m/s ²
Vibration Uncertainty (K Factor), Cutting Wooden Beam	2,0 m/s ²

User benefits

- Tool-less blade change and shoe adjustment
- Brushless maintenance-free and long-life motor
- Wide hanging hook, e.g. for scaffolding
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection system automatically shuts off power when the battery level is low

EAN 0088381893237

Link to product - www.makitauk.com



Related products

Standard AC

194253-2

Recipro Saw Blade Set



Optional AC

412393-7

Battery Cover For Xgt® Batteries



821796-8

Plastic Carrying case



B-05038

Reciprosaw Blade 152 x 0,9 mm



B-05044

Reciprosaw Blade 152 x 0,9 mm



B-05153

Reciprosaw Blade 203 x 1,0 mm



Other

User manual

Parts drawing